





INCH

METRIC

1. Kennametal Grooving Modular		3. Hand of Tool	4. Shank Dimensions	5. Blade Size	N = inch 6. Tool Units	
KGM		R	16	50	N	
2. Tool Style			25	25	M	
S			4. Shank Height	5. Shank Width	6. Tool Length	
					over insert in a support blade with a 12,5 mm D dimension M = 150 mm P = 170 mm	
E			shank height in millimeters	shank width in millimeters		
					7. Blade Size	
					50	

