



 KENDEX SCREW-ON						
 TOP NOTCH Profiling KENLOC						
1. Insert Holding Method		2. Insert Shape			5. Hand of Tool	
Example:						
M		C			N	
		L			R	
3. Tool Style or Lead Angle					4. Insert Clearance Angle	
A 	B 	C 	D 	E 	N 	D
F 	G 	H 	J 	K 	B 	E
L 	M 	P 	Q 	R 	C 	F
S 	U 	V 	Y 		P 	

*Kennametal standard only



Cartridge Mounting Dimensions



NOTE: All dimensions below in mm

Size of cartridge	H1	h1	Dmin	D	a	b	[MHD]	F	k	r	[MHH]	[MHD2]	[MHA]	[G5]
06	6	2,0	20	17	10	11	12	8	12,0	4,0	3,5	-	20	M 3,5 x 0,60
08	8	2,5	25	22	10	14	17	10	18,5	5,0	4,5	-	20	M 4,0 x 0,70
10	10	6,0	40	37	14	16	20	14	26,0	8,0	5,0	-	20	M 6,0 x 1,00
12	12	5,0	50	47	14	21	20	20	28,0	9,5	6,0	-	20	M 6,0 x 1,00
16	16	5,0	60	57	15	24	25	25	34,0	9,5	-	-	45	M 8,0 x 1,25
20	20	10,0	70	67	15	31	30	25	36,0	9,5	-	-	45	M 8,0 x 1,25
25	25	18,0	100	97	19	36	30	32	60,0	12,5	-	20	45	M10,0 x 1,50