



SAFETY DATA SHEET

Issuing Date 17-Oct-2014

Revision Date 07-Sep-2018

Revision Number 2

1. IDENTIFICATION OF THE SUBSTANCE/PREPARATION AND THE COMPANY/UNDERTAKING

GHS product identifier

Product Name Door-Ease Compound

Other means of identification

Product Code(s) CEK-3OL, DE-1, DE-2, DE-25, DE-3, DEB-2, DEB-3, DEC-3, DEK-3, DEK-3BK (765-1385), DEK-3H, DEP-1, DEP-3, DKC-3, DR-2, DR-2CH, DR-2GG, TA-2, TA-2ML, TM-2, TM-2BG, TM-2BR, TM-2PP, ZE-2 N/C, ZE-2CGC, ZE-2CS, ZE-2IS, ZE-2TD, ZE-2CGF

Synonyms Door-Ease, Drill-Ease, Tap-Ease, Trim-Ease, Zipper-Ease

Recommended use of the chemical and restrictions on use

Recommended Use Sliding door and window channels, curtain rod slides, latches, doors, drawers, zippers, sunroofs, seat tracks, screws and nails, and power and handsaw blades, drill bits for all types of drilling applications, all types of tap and die applications, use in the trimming of plastic laminates, metal or plastic zipper teeth of garments, outdoor equipment, sports equipment, wet suits, tarps, upholstery.

Uses advised against No information available

Supplier's details

Supplier Address

AGS Company
Automotive Solutions LLC
P.O. Box 729
Muskegon, MI
49443
TEL: 800-253-0403

Emergency telephone number

Emergency Telephone Number 800-255-3924

2. HAZARDS IDENTIFICATION

Classification

This product is not considered hazardous by the OSHA Hazard Communication Standard 2012 (29 CFR 1910.1200).

GHS Label elements, including precautionary statements

Emergency Overview

Signal Word	None		
Hazard Statements	None The product contains no substances which at their given concentration are considered to be hazardous to health		
Appearance	Tan, Wax.	Physical State	Semi-Solid.
		Odor	Petroleum.

Precautionary Statements**Prevention**

- None

General Advice

- None

Storage

- None

Disposal

- None

Hazard Not Otherwise Classified (HNOC)

Not applicable.

Other information

None known.

Unknown acute toxicity

6.9707% of the mixture consists of ingredient(s) of unknown toxicity.

3. COMPOSITION/INFORMATION ON INGREDIENTS

Synonyms

Door-Ease, Drill-Ease, Tap-Ease, Trim-Ease, Zipper-Ease

Chemical Name	CAS-No	Weight %	Trade secret
Petroleum distillates, hydrotreated heavy naphthenic	64742-52-5	15-40	*
Paraffin	8002-74-2	15-40	*
Microcrystalline wax	63231-60-7	10-30	*
Tallow oil	61789-97-7	1-5	*
Carnauba wax	8015-86-9	1-5	*
Neodecanoic acid, zinc salt	27253-29-8	0.1-1	*
Naphthenic acids, zinc salts	12001-85-3	0.1-1	*
Polyethylene	9002-88-4	0.1-1	*
Petroleum distillates, hydrotreated middle	64742-46-7	0.1-1	*

*The exact percentage (concentration) of composition has been withheld as a trade secret.

4. FIRST AID MEASURES

Description of necessary first-aid measures**Eye Contact**

Rinse thoroughly with plenty of water for at least 15 minutes and consult a physician.

Skin Contact

Wash skin with soap and water.

Inhalation

Move to fresh air.

Ingestion Clean mouth with water and afterwards drink plenty of water.

Most important symptoms/effects, acute and delayed

Most Important Symptoms/Effects No information available

Indication of immediate medical attention and special treatment needed, if necessary

Notes to Physician Treat symptomatically.

5. FIRE-FIGHTING MEASURES

Suitable Extinguishing Media

Use extinguishing measures that are appropriate to local circumstances and the surrounding environment.

Unsuitable Extinguishing Media No information available

Specific Hazards Arising from the Chemical

No information available.

Explosion Data

Sensitivity to Mechanical Impact

None.

Sensitivity to Static Discharge

None.

Protective Equipment and Precautions for Firefighters

As in any fire, wear self-contained breathing apparatus pressure-demand, MSHA/NIOSH (approved or equivalent) and full protective gear.

6. ACCIDENTAL RELEASE MEASURES

Personal precautions, protective equipment and emergency procedures

Personal Precautions Ensure adequate ventilation.

Environmental Precautions

Environmental Precautions See Section 12 for additional Ecological Information.

Methods and materials for containment and cleaning up

Methods for Containment Prevent further leakage or spillage if safe to do so.

Methods for Cleaning Up Pick up and transfer to properly labeled containers.

7. HANDLING AND STORAGE

Precautions for safe handling

Handling Handle in accordance with good industrial hygiene and safety practice.

Conditions for safe storage, including any incompatibilities

Storage Keep containers tightly closed in a dry, cool and well-ventilated place.

Incompatible Products None known based on information supplied.

8. EXPOSURE CONTROLS / PERSONAL PROTECTION

Control parameters

Exposure Guidelines

Chemical Name	ACGIH TLV	OSHA PEL	NIOSH IDLH
Paraffin 8002-74-2	TWA: 2 mg/m ³	(vacated) TWA: 2 mg/m ³	TWA: 2 mg/m ³

Appropriate engineering controls

Engineering Measures

Showers
Eyewash stations
Ventilation systems

Individual protection measures, such as personal protective equipment

Eye/Face Protection None required for consumer use. If direct contact possible: Safety glasses with side-shields.
Skin and Body Protection None required for consumer use. If direct contact possible: Wear protective gloves/clothing.
Respiratory Protection If exposure limits are exceeded or irritation is experienced, NIOSH/MSHA approved respiratory protection should be worn. Positive-pressure supplied air respirators may be required for high airborne contaminant concentrations. Respiratory protection must be provided in accordance with current local regulations.

Hygiene Measures Handle in accordance with good industrial hygiene and safety practice.

9. PHYSICAL AND CHEMICAL PROPERTIES

Information on basic physical and chemical properties

Physical State	Semi-Solid.	Appearance	Tan, Wax.
Odor	Petroleum.	Odor Threshold	No information available.

<u>Property</u>	<u>Values</u>	<u>Remarks/ - Method</u>
pH	Not applicable	None known
Melting Point/Range	72 °C / 162 °F	None known
Boiling Point/Boiling Range	300 °C / 572 °F	None known
Flash Point	193 °C / 379 °F	Cleveland Open Cup (COC)
Evaporation rate	Slower than Butyl Acetate	None known
Flammability (solid, gas)	No data available	None known
Flammability Limits in Air		
upper flammability limit	No data available	
lower flammability limit	No data available	
Vapor Pressure	No data available	None known
Vapor Density	Heavier than air	None known
Specific Gravity	0.75	None known
Water Solubility	Insoluble in water.	None known
Solubility in other solvents	No data available	None known
Partition coefficient: n-octanol/water	Negligible	None known
Autoignition Temperature	No data available	None known
Decomposition Temperature	No data available	None known
Viscosity	No data available	None known

Flammable Properties No data available.

Explosive Properties No data available
Oxidizing Properties No data available

Other information

VOC Content (%) 0

10. STABILITY AND REACTIVITY

Reactivity

No data available.

Chemical stability

Stable under recommended storage conditions.

Possibility of hazardous reactions

None under normal processing.

Hazardous Polymerization

Hazardous polymerization does not occur.

Conditions to avoid

None known based on information supplied.

Incompatible materials

None known based on information supplied.

Hazardous decomposition products

None known based on information supplied.

11. TOXICOLOGICAL INFORMATION

Information on likely routes of exposure

Product Information	There is no data available for this product
Inhalation	There is no data available for this product.
Eye Contact	There is no data available for this product.
Skin Contact	There is no data available for this product.
Ingestion	There is no data available for this product.

Symptoms related to the physical, chemical and toxicological characteristics

Symptoms No information available.

Delayed and immediate effects and also chronic effects from short and long term exposure

Sensitization	No information available
Mutagenic Effects	No information available
Carcinogenicity	The table below indicates whether each agency has listed any ingredient as a carcinogen.

Chemical Name	ACGIH	IARC	NTP	OSHA
Polyethylene		Group 3		

Reproductive Toxicity	No information available
STOT - single exposure	No information available
STOT - repeated exposure	No information available
Aspiration Hazard	No information available.

Numerical measures of toxicity - Product

Unknown acute toxicity 6.9707% of the mixture consists of ingredient(s) of unknown toxicity.

The following values are calculated based on chapter 3.1 of the GHS document:

LD50 Oral	5960 mg/kg; Acute toxicity estimate
LD50 Dermal	4706 mg/kg; Acute toxicity estimate

12. ECOLOGICAL INFORMATION

Ecotoxicity

The environmental impact of this product has not been fully investigated.

Chemical Name	Toxicity to Algae	Toxicity to Fish	Toxicity to Microorganisms	Daphnia Magna (Water Flea)
Petroleum distillates, hydrotreated heavy naphthenic 64742-52-5		LC50 96 h: > 5000 mg/L (Oncorhynchus mykiss)		EC50 48 h: > 1000 mg/L (Daphnia magna)
Petroleum distillates, hydrotreated middle 64742-46-7		LC50: 35 mg/L Pimephales promelas 96 h flow-through LC50: >10000 mg/L Pimephales promelas 96 h static		

Persistence and Degradability No information available

Bioaccumulation

Chemical Name	Log Pow
Microcrystalline wax	6.006

Other Adverse Effects

No information available.

13. DISPOSAL CONSIDERATIONS

Waste Disposal Methods

This material, as supplied, is not a hazardous waste according to Federal regulations (40 CFR 261). This material could become a hazardous waste if it is mixed with or otherwise comes in contact with a hazardous waste, if chemical additions are made to this material, or if the material is processed or otherwise altered. Consult 40 CFR 261 to determine whether the altered material is a hazardous waste. Consult the appropriate state, regional, or local regulations for additional requirements.

Contaminated Packaging

Do not re-use empty containers.

14. TRANSPORT INFORMATION

<u>DOT</u>	Not regulated
<u>TDG</u>	Not regulated
<u>MEX</u>	Not regulated
<u>ICAO</u>	Not regulated
<u>IATA</u>	Not regulated
<u>IMDG/IMO</u>	Not regulated
<u>RID</u>	Not regulated
<u>ADR</u>	Not regulated
<u>ADN</u>	Not regulated

15. REGULATORY INFORMATION

International Inventories

TSCA	Contact supplier for inventory compliance status
DSL/NDSL	Contact supplier for inventory compliance status

Legend

TSCA - United States Toxic Substances Control Act Section 8(b) Inventory

DSL/NDSL - Canadian Domestic Substances List/Non-Domestic Substances List

U.S. Federal Regulations

Section 313 of Title III of the Superfund Amendments and Reauthorization Act of 1986 (SARA). This product does not contain any chemicals which are subject to the reporting requirements of the Act and Title 40 of the Code of Federal Regulations, Part 372.

SARA 311/312 Hazard Categories

Should this product meet EPCRA 311/312 Tier reporting criteria at 40 CFR 370, refer to Section 2 of this SDS for appropriate classifications. Under the amended regulations at 40 CFR 370, EPCRA 311/312 Tier II reporting for the 2017 calendar year will need to be consistent with updated hazard classifications.

Clean Water Act

This product contains the following substances which are regulated pollutants pursuant to the Clean Water Act (40 CFR 122.21 and 40 CFR 122.42):

Chemical Name	CWA - Reportable Quantities	CWA - Toxic Pollutants	CWA - Priority Pollutants	CWA - Hazardous Substances
Neodecanoic acid, zinc salt		X		
Naphthenic acids, zinc salts		X		

CERCLA

This material, as supplied, does not contain any substances regulated as hazardous substances under the Comprehensive Environmental Response Compensation and Liability Act (CERCLA) (40 CFR 302) or the Superfund Amendments and Reauthorization Act (SARA) (40 CFR 355). There may be specific reporting requirements at the local, regional, or state level pertaining to releases of this material.

U.S. State Regulations**California Proposition 65**

This product does not contain any Proposition 65 chemicals.

U.S. State Right-to-Know Regulations

Chemical Name	New Jersey	Massachusetts	Pennsylvania	Illinois	Rhode Island
Petroleum distillates, hydrotreated heavy naphthenic				X	
Paraffin	X	X	X	-	X
Tallow oil					X

U.S. EPA Label Information

EPA Pesticide Registration Number Not applicable

16. OTHER INFORMATION

<u>NFPA</u>	Health Hazard 1	Flammability 0	Instability 0	Physical and Chemical Hazards -
<u>HMIS</u>	Health Hazard 1	Flammability 0	Physical Hazard 0	Personal Protection X

Prepared By Product Stewardship
23 British American Blvd.
Latham, NY 12110
1-800-572-6501

Issuing Date 17-Oct-2014

Revision Date 07-Sep-2018

Revision Note Initial Release.

General Disclaimer

The information provided on this SDS is correct to the best of our knowledge, information and belief at the date of its publication. The information given is designed only as a guide for safe handling, use, processing, storage, transportation, disposal and release and is not to be considered as a warranty or quality specification. The information relates only to the specific material designated and may not be valid for such material used in combination with any other material or in any process, unless specified in the text.

End of Safety Data Sheet