



Safety Data Sheet

Copyright, 2014, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	20-1896-8	Version Number:	5.05
Issue Date:	03/21/14	Supersedes Date:	03/14/14

SECTION 1: Identification

1.1. Product identifier

3M™ Scotch-Brite™ Products, MultiFlex Type A

1.2. Recommended use and restrictions on use

Recommended use

Abrasive Product

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Abrasive Systems Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

2.2. Label elements

Signal word

Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

2.3. Hazards not otherwise classified

None.

65% of the mixture consists of ingredients of unknown acute oral toxicity.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Aluminum Oxide Mineral (non-fibrous)	1344-28-1	30 - 45
Filler	1317-65-3	2 - 5
Titanium Dioxide	13463-67-7	< 2
Carbon Black	1333-86-4	< 0.3
Cured Resin	Mixture	15 - 50
Nylon Fiber	Mixture	20 - 30

SECTION 4: First aid measures**4.1. Description of first aid measures****Inhalation:**

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

No need for first aid is anticipated.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures**5.1. Suitable extinguishing media**

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products**Substance**

Amine Compounds

Carbon monoxide

Carbon dioxide

Hydrogen Cyanide

Ammonia

Oxides of Nitrogen

Condition

During Combustion

During Combustion

During Combustion

During Combustion

During Combustion

During Combustion

5.3. Special protective actions for fire-fighters

No unusual fire or explosion hazards are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

Observe precautions from other sections.

6.2. Environmental precautions

Not applicable.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

Avoid breathing of dust created by sanding, grinding or machining. Combustible dust may form by action of this product on another material (substrate). Dust generated from the substrate during use of this product may be explosive if in sufficient concentration with an ignition source. Dust deposits should not be allowed to accumulate on surfaces because of the potential for secondary explosions.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Filler	1317-65-3	US Dept of Labor - OSHA	TWA(as total dust):15 mg/m3;TWA(respirable fraction):5 mg/m3	
Carbon Black	1333-86-4	Amer Conf of Gov. Indust. Hyg.	TWA(inhalable fraction):3 mg/m3	
Carbon Black	1333-86-4	Chemical Manufacturer Rec Guid	TWA:0.5 mg/m3	
Carbon Black	1333-86-4	US Dept of Labor - OSHA	TWA:3.5 mg/m3	
Aluminum Oxide Mineral (non-fibrous)	1344-28-1	Chemical Manufacturer Rec Guid	TWA:1 fiber/cc	
Aluminum Oxide Mineral (non-fibrous)	1344-28-1	US Dept of Labor - OSHA	TWA(as total dust):15 mg/m3;TWA(respirable fraction):5 mg/m3	
Aluminum, insoluble compounds	1344-28-1	Amer Conf of Gov. Indust. Hyg.	TWA(respirable fraction):1 mg/m3	
Titanium Dioxide	13463-67-7	Amer Conf of Gov. Indust. Hyg.	TWA:10 mg/m3	
Titanium Dioxide	13463-67-7	Chemical Manufacturer	TWA(as respirable dust):5 mg/m3	

		Rec Guid		
Titanium Dioxide	13463-67-7	US Dept of Labor - OSHA	TWA(as total dust):15 mg/m3	

Amer Conf of Gov. Indust. Hyg. : American Conference of Governmental Industrial Hygienists

American Indust. Hygiene Assoc : American Industrial Hygiene Association

Chemical Manufacturer Rec Guid : Chemical Manufacturer's Recommended Guidelines

US Dept of Labor - OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit

CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment. Warning: Excessive operating speed or generation of extreme heat may result in harmful emissions. Use local exhaust ventilation. Provide local exhaust at process emission sources to control exposure near the source and to prevent the escape of dust into the work area. Ensure that dust-handling systems (such as exhaust ducts, dust collectors, vessels, and processing equipment) are designed in a manner to prevent the escape of dust into the work area (i.e., there is no leakage from the equipment).

8.2.2. Personal protective equipment (PPE)

Eye/face protection

To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:

Safety Glasses with side shields

Skin/hand protection

Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

Respiratory protection

Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure. An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:

Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form: Solid

Odor, Color, Grade: Solid Abrasive Product

Odor threshold: Not Applicable

pH: Not Applicable

Melting point: Not Applicable

Boiling Point	Not Applicable
Flash Point	Not Applicable
Evaporation rate	Not Applicable
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	Not Applicable
Flammable Limits(UEL)	Not Applicable
Vapor Pressure	Not Applicable
Vapor Density	Not Applicable
Density	Not Applicable
Specific Gravity	Not Applicable
Solubility In Water	Not Applicable
Solubility- non-water	Not Applicable
Partition coefficient: n-octanol/ water	Not Applicable
Autoignition temperature	Not Applicable
Decomposition temperature	Not Applicable
Viscosity	Not Applicable

SECTION 10: Stability and reactivity

10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

Substance

None known.

Condition

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Ingestion:

No health effects are expected.

Carcinogenicity:

<u>Ingredient</u>	<u>C.A.S. No.</u>	<u>Class Description</u>	<u>Regulation</u>
Carbon Black	1333-86-4	Grp. 2B: Possible human carc.	International Agency for Research on Cancer
Titanium Dioxide	13463-67-7	Grp. 2B: Possible human carc.	International Agency for Research on Cancer

Additional Information:

This document covers only the 3M product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered.

This product contains titanium dioxide. Cancer of the lungs has been observed in rats that inhaled high levels of titanium dioxide. No exposure to inhaled titanium dioxide is expected during the normal handling and use of this product. Titanium dioxide was not detected when air sampling was conducted during simulated use of similar products containing titanium dioxide. Therefore, the health effects associated with titanium dioxide are not expected during the normal use of this product.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

<u>Name</u>	<u>Route</u>	<u>Species</u>	<u>Value</u>
Overall product	Ingestion		No data available; calculated ATE > 5,000 mg/kg
Aluminum Oxide Mineral (non-fibrous)	Dermal		LD50 estimated to be > 5,000 mg/kg
Aluminum Oxide Mineral (non-fibrous)	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 2.3 mg/l
Aluminum Oxide Mineral (non-fibrous)	Ingestion	Rat	LD50 > 5,000 mg/kg
Filler	Dermal	Rat	LD50 > 2,000 mg/kg
Filler	Inhalation-Dust/Mist (4 hours)	Rat	LC50 3.0 mg/l
Filler	Ingestion	Rat	LD50 6,450 mg/kg
Titanium Dioxide	Dermal	Rabbit	LD50 > 10,000 mg/kg
Titanium Dioxide	Inhalation-Dust/Mist (4 hours)	Rat	LC50 > 6.82 mg/l
Titanium Dioxide	Ingestion	Rat	LD50 > 10,000 mg/kg

Carbon Black	Dermal	Rabbit	LD50 > 3,000 mg/kg
Carbon Black	Ingestion	Rat	LD50 > 8,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

Name	Species	Value
Aluminum Oxide Mineral (non-fibrous)	Rabbit	No significant irritation
Filler	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation
Carbon Black	Rabbit	No significant irritation

Serious Eye Damage/Irritation

Name	Species	Value
Aluminum Oxide Mineral (non-fibrous)	Rabbit	No significant irritation
Filler	Rabbit	No significant irritation
Titanium Dioxide	Rabbit	No significant irritation
Carbon Black	Rabbit	No significant irritation

Skin Sensitization

Name	Species	Value
Titanium Dioxide	Human and animal	Not sensitizing

Respiratory Sensitization

Name	Species	Value

Germ Cell Mutagenicity

Name	Route	Value
Aluminum Oxide Mineral (non-fibrous)	In Vitro	Not mutagenic
Titanium Dioxide	In Vitro	Not mutagenic
Titanium Dioxide	In vivo	Not mutagenic
Carbon Black	In Vitro	Not mutagenic
Carbon Black	In vivo	Some positive data exist, but the data are not sufficient for classification

Carcinogenicity

Name	Route	Species	Value
Aluminum Oxide Mineral (non-fibrous)	Inhalation	Rat	Not carcinogenic
Titanium Dioxide	Ingestion	Multiple animal species	Not carcinogenic
Titanium Dioxide	Inhalation	Rat	Carcinogenic
Carbon Black	Dermal	Mouse	Not carcinogenic
Carbon Black	Ingestion	Mouse	Not carcinogenic
Carbon Black	Inhalation	Rat	Carcinogenic

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Filler	Ingestion	Not toxic to development	Rat	NOAEL 625 mg/kg/day	prematuring & during gestation

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration

Filler	Inhalation	respiratory system	All data are negative	Rat	NOAEL 0.812 mg/l	90 minutes
--------	------------	--------------------	-----------------------	-----	---------------------	------------

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Aluminum Oxide Mineral (non-fibrous)	Inhalation	pneumoconiosis pulmonary fibrosis	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure
Filler	Inhalation	respiratory system	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure
Titanium Dioxide	Inhalation	respiratory system	Some positive data exist, but the data are not sufficient for classification	Rat	LOAEL 0.010 mg/l	2 years
Titanium Dioxide	Inhalation	pulmonary fibrosis	All data are negative	Human	NOAEL Not available	occupational exposure
Carbon Black	Inhalation	pneumoconiosis	Some positive data exist, but the data are not sufficient for classification	Human	NOAEL Not available	occupational exposure

Aspiration Hazard

Name	Value

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information**Ecotoxicological information**

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations**13.1. Disposal methods**

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. The substrate that was abraded must be considered as a factor in the disposal method for this product. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. If no other disposal options are available, waste product may be placed in a landfill properly designed for industrial waste.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

Not regulated per U.S. DOT, IATA or IMO.

These transportation classifications are provided as a customer service. As the shipper YOU remain responsible for complying with all applicable laws and regulations, including proper transportation classification and packaging. 3M transportation classifications are based on product formulation, packaging, 3M policies and 3M understanding of

*applicable current regulations. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and **not the packaging, labeling, or marking requirements**. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.*

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

311/312 Hazard Categories:

Fire Hazard - No Pressure Hazard - No Reactivity Hazard - No Immediate Hazard - No Delayed Hazard - No

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 0 **Flammability:** 1 **Physical Hazard:** 0 **Personal Protection:** X - See PPE section.

Hazardous Material Identification System (HMIS® III) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® III ratings are to be used with a fully implemented HMIS® III program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group:	20-1896-8	Version Number:	5.05
Issue Date:	03/21/14	Supersedes Date:	03/14/14

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable

for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com