

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

1 Identification

- **Product identifier**
- **Trade name:** Starrett Tool & Instrument Oil
- **Article number:** No other identifiers
- **Recommended use and restriction on use**
- **Recommended use:** Lubricant
- **Restrictions on use:** Contact manufacturer
- **Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
The L.S. Starrett Company
121 Crescent St.
Athol, MA 01331
(978) 249-3551
- **Emergency telephone number:**
ChemTel Inc.
+1 (800)255-3924, +1 (813)248-0585

2 Hazard(s) identification

- **Classification of the substance or mixture**
Asp. Tox. 1 H304 May be fatal if swallowed and enters airways.
- **Additional information:**
There are no other hazards not otherwise classified that have been identified.
0 % of the mixture consists of component(s) of unknown toxicity.
- **Label elements**
- **GHS label elements**
The substance is classified and labeled according to the Globally Harmonized System (GHS).
The product is classified and labeled according to the Globally Harmonized System (GHS).
- **Hazard pictograms:**

GHS08
- **Signal word:** Danger
- **Hazard statements:**
H304 May be fatal if swallowed and enters airways.
- **Precautionary statements:**
P301+P310 IF SWALLOWED: Immediately call a POISON CENTER/ doctor.
P331 Do NOT induce vomiting.
P405 Store locked up.
P501 Dispose of contents/container in accordance with local/regional/national/international regulations.

(Cont'd. on page 2)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 1)

- **Classification system**
- **NFPA ratings (scale 0 - 4)**



Health = 0
Fire = 1
Reactivity = 0

- **HMIS-ratings (scale 0 - 4)**



Health = 0
Fire = 1
Reactivity = 0

3 Composition/information on ingredients

- **Chemical characterization: Mixtures**

- **Components:**

8042-47-5 | White Mineral Oil



Asp. Tox. 1, H304

>80%

- **Additional information:**

For the listed ingredient(s), the identity and/or exact percentage(s) are being withheld as a trade secret.
For the wording of the listed Hazard Statements refer to section 16.

4 First-aid measures

- **Description of first aid measures**

- **General information:**

Position and transport stably on side.

Take affected persons out into the fresh air.

- **After inhalation:**

Supply fresh air; consult doctor in case of complaints.

In case of unconsciousness place patient stably in side position for transportation.

- **After skin contact:**

Wash with soap and water.

If skin irritation is experienced, consult a doctor.

- **After eye contact:**

Remove contact lenses if worn.

Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.

- **After swallowing:**

Rinse out mouth and then drink plenty of water.

A person vomiting while lying on their back should be turned onto their side.

Do not induce vomiting; immediately call for medical help.

- **Most important symptoms and effects, both acute and delayed:** Gastric or intestinal disorders

- **Danger:**

May be fatal if swallowed and enters airways.

Danger of pulmonary edema.

Danger of impaired breathing.

(Cont'd. on page 3)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 2)

· Indication of any immediate medical attention and special treatment needed:

If swallowed, gastric irrigation with added, activated carbon.

If swallowed or in case of vomiting, danger of entering the lungs.

Medical supervision for at least 48 hours.

5 Fire-fighting measures

· Extinguishing media**· Suitable extinguishing agents:**

Foam

Gaseous extinguishing agents

Carbon dioxide

Fire-extinguishing powder

· For safety reasons unsuitable extinguishing agents: Water**· Special hazards arising from the substance or mixture**

Formation of toxic gases is possible during heating or in case of fire.

· Advice for firefighters**· Protective equipment:**

Wear self-contained respiratory protective device.

Wear fully protective suit.

· Additional information: No relevant information available.

6 Accidental release measures

· Personal precautions, protective equipment and emergency procedures:

Ensure adequate ventilation.

Wear protective clothing.

For large spills, use respiratory protective device against the effects of fumes/dust/aerosol.

Particular danger of slipping on leaked/spilled product.

· Environmental precautions: Do not allow to enter sewers/ surface or ground water.**· Methods and material for containment and cleaning up:**

Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).

Dispose contaminated material as waste according to item 13.

Send for recovery or disposal in suitable receptacles.

· Reference to other sections:

See Section 7 for information on safe handling.

See Section 8 for information on personal protection equipment.

See Section 13 for disposal information.

7 Handling and storage

· Handling**· Precautions for safe handling:**

Prevent formation of aerosols.

Avoid splashes or spray in enclosed areas.

(Cont'd. on page 4)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 3)

Use only in well ventilated areas.

- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:**
Avoid storage near extreme heat, ignition sources or open flame.
Provide ventilation for receptacles.
- **Information about storage in one common storage facility:** Store away from foodstuffs.
- **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s):** No relevant information available.

8 Exposure controls/personal protection

- **Control parameters**
 - **Components with limit values that require monitoring at the workplace:**
The product does not contain any relevant quantities of materials with critical values that have to be monitored at the workplace.
 - **Exposure controls**
 - **Personal protective equipment:**
 - **General protective and hygienic measures:**
The usual precautionary measures for handling chemicals should be followed.
Be sure to clean skin thoroughly after work and before breaks.
Keep away from foodstuffs, beverages and feed.
Wash hands before breaks and at the end of work.
Do not inhale gases / fumes / aerosols.
Avoid contact with the eyes.
 - **Engineering controls:** No relevant information available.
 - **Breathing equipment:**
Use suitable respiratory protective device when aerosol or mist is formed.
Use suitable respiratory protective device when high concentrations are present.
 - **Protection of hands:** Rubber gloves
 - **Eye protection:**
- 

Safety glasses
- **Body protection:**
Not required under normal conditions of use.
Protection may be required for spills.
 - **Limitation and supervision of exposure into the environment**
No relevant information available.

(Cont'd. on page 5)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 4)

9 Physical and chemical properties

· Information on basic physical and chemical properties

· Appearance:

Form: Liquid

Color: Clear

· Odor: Light

· Odor threshold: Not determined.

· pH-value: Not determined.

· Melting point/Melting range: Not determined.

· Boiling point/Boiling range: Not determined.

· Flash point: 188 °C (370 °F)

· Flammability (solid, gaseous): Not applicable.

· Auto-ignition temperature: Not determined.

· Decomposition temperature: Not determined.

· Danger of explosion: Product does not present an explosion hazard.

· Explosion limits

Lower: Not determined.

Upper: Not determined.

· Vapor pressure: Not determined.

· Density: Not determined.

· Relative density: Not determined.

· Vapor density: Not determined.

· Evaporation rate: Not determined.

· Solubility in / Miscibility with

Water: Not miscible or difficult to mix.

· Partition coefficient (n-octanol/water): Not determined.

· Viscosity

Dynamic: Not determined.

Kinematic: Not determined.

· Other information: No relevant information available.

10 Stability and reactivity

· **Reactivity:** No relevant information available.· **Chemical stability:**· **Thermal decomposition / conditions to be avoided:**

No decomposition if used according to specifications.

· **Possibility of hazardous reactions:** Reacts with strong oxidizing agents.· **Conditions to avoid:** No relevant information available.· **Incompatible materials:** No relevant information available.

(Cont'd. on page 6)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 5)

· **Hazardous decomposition products:** Carbon monoxide and carbon dioxide

11 Toxicological information

· Information on toxicological effects

- **Acute toxicity:**
- **LD/LC50 values that are relevant for classification:** None.
- **Primary irritant effect:**
- **On the skin:** No irritant effect.
- **On the eye:** Slight irritant effect on eyes.
- **Sensitization:** No sensitizing effects known.
- **Subacute to chronic toxicity:** May be fatal if swallowed and enters airways.

· **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

· **NTP (National Toxicology Program):**

None of the ingredients are listed.

· **OSHA-Ca (Occupational Safety & Health Administration):**

None of the ingredients are listed.

· **Probable route(s) of exposure:**

Ingestion.
Inhalation.
Eye contact.
Skin contact.

- **Acute effects (acute toxicity, irritation and corrosivity):** May be fatal if swallowed and enters airways.
- **Repeated dose toxicity:** From product as supplied: None.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.
- **Carcinogenicity:** Based on available data, the classification criteria are not met.
- **Reproductive toxicity:** Based on available data, the classification criteria are not met.
- **STOT-single exposure:** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.
- **Aspiration hazard:** May be fatal if swallowed and enters airways.

12 Ecological information

· **Toxicity**

- **Aquatic toxicity** No relevant information available.
- **Persistence and degradability** No relevant information available.
- **Bioaccumulative potential:** No relevant information available.
- **Mobility in soil:** No relevant information available.

· **Additional ecological information**

· **General notes:**

Do not allow undiluted product or large quantities of it to reach ground water, water course or sewage system.

(Cont'd. on page 7)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 6)

- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects:** No relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Product is recyclable as a waste oil. Deliver unused and/or contaminated product to waste oil collectors. Must not be disposed of together with household garbage. Do not allow product to reach sewage system. The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.
- **Uncleaned packagings**
- **Recommendation:** Disposal must be made according to official regulations.

14 Transport information

- | | |
|--|-----------------|
| · UN-Number | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · UN proper shipping name | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · Transport hazard class(es) | |
| · DOT, ADR, IMDG, IATA | |
| · Class | Not regulated. |
| · Packing group | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · Environmental hazards | |
| · Marine pollutant: | No |
| · Special precautions for user | Not applicable. |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |

(Cont'd. on page 8)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 7)

15 Regulatory information

- Safety, health and environmental regulations/legislation specific for the substance or mixture
- United States (USA)
- SARA

- **Section 355 (extremely hazardous substances):**

None of the ingredients are listed.

- **Section 313 (Specific toxic chemical listings):**

None of the ingredients are listed.

- **TSCA (Toxic Substances Control Act)**

All ingredients are listed.

- **Proposition 65 (California)**

- **Chemicals known to cause cancer:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients are listed.

- **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients are listed.

- **Chemicals known to cause developmental toxicity:**

None of the ingredients are listed.

- **Carcinogenic categories**

- **EPA (Environmental Protection Agency):**

None of the ingredients are listed.

- **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

- **NIOSH-Ca (National Institute for Occupational Safety and Health):**

None of the ingredients are listed.

- **Canadian Domestic Substances List (DSL):**

All ingredients are listed.

- **Chemical safety assessment:** A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

- **Date of preparation / last revision** 04/22/2016 / -

- **Abbreviations and acronyms:**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

(Cont'd. on page 9)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Tool & Instrument Oil

(Cont'd. of page 8)

IATA: International Air Transport Association
GHS: Globally Harmonised System of Classification and Labelling of Chemicals
ACGIH: American Conference of Governmental Industrial Hygienists
CAS: Chemical Abstracts Service (division of the American Chemical Society)
NFPA: National Fire Protection Association (USA)
HMIS: Hazardous Materials Identification System (USA)
DNEL: Derived No-Effect Level (REACH)
PNEC: Predicted No-Effect Concentration (REACH)
LC50: Lethal concentration, 50 percent
LD50: Lethal dose, 50 percent
Asp. Tox. 1: Aspiration hazard, Hazard Category 1

• Sources

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com