



Safety Data Sheet

Copyright, 2018, 3M Company.

All rights reserved. Copying and/or downloading of this information for the purpose of properly utilizing 3M products is allowed provided that: (1) the information is copied in full with no changes unless prior written agreement is obtained from 3M, and (2) neither the copy nor the original is resold or otherwise distributed with the intention of earning a profit thereon.

Document Group:	26-6692-3	Version Number:	1.19
Issue Date:	03/05/18	Supersedes Date:	05/19/15

SECTION 1: Identification

1.1. Product identifier

3M™ Scotch-Brite™ Products, EXL Unitized S FIN, S MED, S VFN Products, Wheels, Blocks, Discs, Roloc™ TR, Roloc™ TS

1.2. Recommended use and restrictions on use

Recommended use

Abrasive Product

1.3. Supplier's details

MANUFACTURER:	3M
DIVISION:	Abrasive Systems Division
ADDRESS:	3M Center, St. Paul, MN 55144-1000, USA
Telephone:	1-888-3M HELPS (1-888-364-3577)

1.4. Emergency telephone number

1-800-364-3577 or (651) 737-6501 (24 hours)

SECTION 2: Hazard identification

2.1. Hazard classification

Not classified as hazardous according to OSHA Hazard Communication Standard, 29 CFR 1910.1200.

2.2. Label elements

Signal word

Not applicable.

Symbols

Not applicable.

Pictograms

Not applicable.

SECTION 3: Composition/information on ingredients

Ingredient	C.A.S. No.	% by Wt
Silicon Carbide Mineral	409-21-2	35 - 55
Lubricant	4485-12-5	2 - 5
Talc	14807-96-6	3 - 10
Lubricant	64742-52-5	0.05 - 0.5
Quartz Silica	14808-60-7	0.02 - 0.25
Cured Resin	Mixture	20 - 35
Nylon Fiber	Mixture	5 - 15
Cloth Backing	Mixture	3 - 8
Attachment Button	Mixture	0 - 5

SECTION 4: First aid measures

4.1. Description of first aid measures

Inhalation:

Remove person to fresh air. If you feel unwell, get medical attention.

Skin Contact:

Wash with soap and water. If signs/symptoms develop, get medical attention.

Eye Contact:

Flush with large amounts of water. Remove contact lenses if easy to do. Continue rinsing. If signs/symptoms persist, get medical attention.

If Swallowed:

No need for first aid is anticipated.

4.2. Most important symptoms and effects, both acute and delayed

See Section 11.1. Information on toxicological effects.

4.3. Indication of any immediate medical attention and special treatment required

Not applicable

SECTION 5: Fire-fighting measures

5.1. Suitable extinguishing media

In case of fire: Use a fire fighting agent suitable for ordinary combustible material such as water or foam to extinguish.

5.2. Special hazards arising from the substance or mixture

None inherent in this product.

Hazardous Decomposition or By-Products

Substance

Carbon monoxide
Carbon dioxide

Condition

During Combustion
During Combustion

5.3. Special protective actions for fire-fighters

No special protective actions for fire-fighters are anticipated.

SECTION 6: Accidental release measures

6.1. Personal precautions, protective equipment and emergency procedures

For large spill, or spills in confined spaces, provide mechanical ventilation to disperse or exhaust vapors, in accordance with good industrial hygiene practice. Observe precautions from other sections.

6.2. Environmental precautions

Not applicable.

6.3. Methods and material for containment and cleaning up

Not applicable.

SECTION 7: Handling and storage

7.1. Precautions for safe handling

For industrial or professional use only. Do not use in a confined area with minimal air exchange. Damaged product can break apart during use and cause serious injury to face or eyes. Check product for damage such as cracks or nicks prior to use. Replace if damaged. Always wear eye and face protection when working at sanding or grinding operations or when near such operations. Combustible dust may form by action of this product on another material (substrate). Dust generated from the substrate during use of this product may be explosive if in sufficient concentration with an ignition source. Dust deposits should not be allowed to accumulate on surfaces because of the potential for secondary explosions.

7.2. Conditions for safe storage including any incompatibilities

No special storage requirements.

SECTION 8: Exposure controls/personal protection

8.1. Control parameters

Occupational exposure limits

If a component is disclosed in section 3 but does not appear in the table below, an occupational exposure limit is not available for the component.

Ingredient	C.A.S. No.	Agency	Limit type	Additional Comments
Talc	14807-96-6	ACGIH	TWA(respirable fraction):2 mg/m3	A4: Not class. as human carcin
Talc	14807-96-6	OSHA	TWA:2 mg/m3	
Quartz Silica	14808-60-7	ACGIH	TWA(respirable fraction):0.025 mg/m3	A2: Suspected human carcin.
Quartz Silica	14808-60-7	OSHA	TWA Table Z-1(respirable):0.05 mg/m3;TWA Table Z-3(respirable):0.1 mg/m3	
Silicon Carbide Mineral	409-21-2	OSHA	TWA(as total dust):15 mg/m3;TWA(respirable fraction):5 mg/m3	
STEARATES	4485-12-5	ACGIH	TWA(inhalable fraction):10 mg/m3;TWA(respirable fraction):3 mg/m3	A4: Not class. as human carcin
Paraffin oil	64742-52-5	OSHA	TWA(as mist):5 mg/m3	
PETROLEUM DISTILLATES	64742-52-5	OSHA	TWA:2000 mg/m3(500 ppm)	

ACGIH : American Conference of Governmental Industrial Hygienists

AIHA : American Industrial Hygiene Association

CMRG : Chemical Manufacturer's Recommended Guidelines

OSHA : United States Department of Labor - Occupational Safety and Health Administration

TWA: Time-Weighted-Average

STEL: Short Term Exposure Limit
CEIL: Ceiling

8.2. Exposure controls

8.2.1. Engineering controls

Provide appropriate local exhaust ventilation for sanding, grinding or machining. Use general dilution ventilation and/or local exhaust ventilation to control airborne exposures to below relevant Exposure Limits and/or control dust/fume/gas/mist/vapors/spray. If ventilation is not adequate, use respiratory protection equipment. Warning: Excessive operating speed or generation of extreme heat may result in harmful emissions. Use local exhaust ventilation. Provide local exhaust at process emission sources to control exposure near the source and to prevent the escape of dust into the work area. Ensure that dust-handling systems (such as exhaust ducts, dust collectors, vessels, and processing equipment) are designed in a manner to prevent the escape of dust into the work area (i.e., there is no leakage from the equipment).

8.2.2. Personal protective equipment (PPE)

Eye/face protection

To minimize the risk of injury to face and eyes, always wear eye and face protection when working at sanding or grinding operations or when near such operations. Select and use eye/face protection to prevent contact based on the results of an exposure assessment. The following eye/face protection(s) are recommended:
Safety Glasses with side shields

Skin/hand protection

Wear appropriate gloves to minimize risk of injury to skin from contact with dust or physical abrasion from grinding or sanding.

Respiratory protection

Assess exposure concentrations of all materials involved in the work process. Consider material being abraded when determining the appropriate respiratory protection. Select and use appropriate respirators to prevent inhalation overexposure. An exposure assessment may be needed to decide if a respirator is required. If a respirator is needed, use respirators as part of a full respiratory protection program. Based on the results of the exposure assessment, select from the following respirator type(s) to reduce inhalation exposure:
Half facepiece or full facepiece air-purifying respirator suitable for particulates

For questions about suitability for a specific application, consult with your respirator manufacturer.

SECTION 9: Physical and chemical properties

9.1. Information on basic physical and chemical properties

General Physical Form:	Solid
Odor, Color, Grade:	Solid Abrasive Product
Odor threshold	<i>Not Applicable</i>
pH	<i>Not Applicable</i>
Melting point	<i>Not Applicable</i>
Boiling Point	<i>Not Applicable</i>
Flash Point	<i>Not Applicable</i>
Evaporation rate	<i>Not Applicable</i>
Flammability (solid, gas)	Not Classified
Flammable Limits(LEL)	<i>Not Applicable</i>
Flammable Limits(UEL)	<i>Not Applicable</i>
Vapor Pressure	<i>Not Applicable</i>
Vapor Density	<i>Not Applicable</i>

Density	Not Applicable
Specific Gravity	Not Applicable
Solubility In Water	Not Applicable
Solubility- non-water	Not Applicable
Partition coefficient: n-octanol/ water	Not Applicable
Autoignition temperature	Not Applicable
Decomposition temperature	Not Applicable
Viscosity	Not Applicable
Molecular weight	No Data Available

SECTION 10: Stability and reactivity

10.1. Reactivity

This material is considered to be non reactive under normal use conditions.

10.2. Chemical stability

Stable.

10.3. Possibility of hazardous reactions

Hazardous polymerization will not occur.

10.4. Conditions to avoid

None known.

10.5. Incompatible materials

None known.

10.6. Hazardous decomposition products

<u>Substance</u>	<u>Condition</u>
None known.	

Refer to section 5.2 for hazardous decomposition products during combustion.

SECTION 11: Toxicological information

The information below may not be consistent with the material classification in Section 2 if specific ingredient classifications are mandated by a competent authority. In addition, toxicological data on ingredients may not be reflected in the material classification and/or the signs and symptoms of exposure, because an ingredient may be present below the threshold for labeling, an ingredient may not be available for exposure, or the data may not be relevant to the material as a whole.

11.1. Information on Toxicological effects

Signs and Symptoms of Exposure

Based on test data and/or information on the components, this material may produce the following health effects:

Inhalation:

Dust from grinding, sanding or machining may cause irritation of the respiratory system. Signs/symptoms may include cough, sneezing, nasal discharge, headache, hoarseness, and nose and throat pain.

Skin Contact:

Mechanical Skin irritation: Signs/symptoms may include abrasion, redness, pain, and itching.

Eye Contact:

Mechanical eye irritation: Signs/symptoms may include pain, redness, tearing and corneal abrasion.

Dust created by grinding, sanding, or machining may cause eye irritation. Signs/symptoms may include redness, swelling, pain, tearing, and blurred or hazy vision.

Ingestion:

No known health effects.

Carcinogenicity:

<u>Ingredient</u>	<u>CAS No.</u>	<u>Class Description</u>	<u>Regulation</u>
SILICA, CRYST AIRRESP	14808-60-7	Known human carcinogen	National Toxicology Program Carcinogens
Quartz Silica	14808-60-7	Grp. 1: Carcinogenic to humans	International Agency for Research on Cancer

Additional Information:

This document covers only the 3M product. For complete assessment, when determining the degree of hazard, the material being abraded must also be considered.

This product contains a form of crystalline silica. Occupational exposure to inhaled crystalline silica has been associated with silicosis and lung cancer. No exposure to crystalline silica is expected during the normal handling and use of this product. Therefore, the health effects associated with crystalline silica are not expected during normal use of this product.

Toxicological Data

If a component is disclosed in section 3 but does not appear in a table below, either no data are available for that endpoint or the data are not sufficient for classification.

Acute Toxicity

<u>Name</u>	<u>Route</u>	<u>Species</u>	<u>Value</u>
Overall product	Ingestion		No data available; calculated ATE >5,000 mg/kg
Silicon Carbide Mineral	Dermal	Rat	LD50 > 2,000 mg/kg
Silicon Carbide Mineral	Ingestion	Rat	LD50 > 2,000 mg/kg
Talc	Dermal		LD50 estimated to be > 5,000 mg/kg
Talc	Ingestion		LD50 estimated to be > 5,000 mg/kg
Lubricant	Dermal		LD50 estimated to be > 5,000 mg/kg
Lubricant	Ingestion	Rat	LD50 > 5,000 mg/kg
Lubricant	Dermal	Rabbit	LD50 > 2,000 mg/kg
Lubricant	Ingestion	Rat	LD50 > 5,000 mg/kg
Quartz Silica	Dermal		LD50 estimated to be > 5,000 mg/kg
Quartz Silica	Ingestion		LD50 estimated to be > 5,000 mg/kg

ATE = acute toxicity estimate

Skin Corrosion/Irritation

<u>Name</u>	<u>Species</u>	<u>Value</u>
Silicon Carbide Mineral	Rat	No significant irritation
Talc	Rabbit	No significant irritation
Lubricant	similar compounds	No significant irritation
Lubricant	Rabbit	Minimal irritation
Quartz Silica	Professional judgement	No significant irritation

	nt	
--	----	--

Serious Eye Damage/Irritation

Name	Species	Value
Silicon Carbide Mineral	Professional judgement	No significant irritation
Talc	Rabbit	No significant irritation
Lubricant	similar compounds	Mild irritant
Lubricant	Rabbit	Mild irritant

Skin Sensitization

Name	Species	Value
Lubricant	Guinea pig	Not classified

Respiratory Sensitization

Name	Species	Value
Talc	Human	Not classified

Germ Cell Mutagenicity

Name	Route	Value
Talc	In Vitro	Not mutagenic
Talc	In vivo	Not mutagenic
Quartz Silica	In Vitro	Some positive data exist, but the data are not sufficient for classification
Quartz Silica	In vivo	Some positive data exist, but the data are not sufficient for classification

Carcinogenicity

Name	Route	Species	Value
Talc	Inhalation	Rat	Some positive data exist, but the data are not sufficient for classification
Lubricant	Ingestion	Rat	Not carcinogenic
Lubricant	Dermal	Mouse	Some positive data exist, but the data are not sufficient for classification
Quartz Silica	Inhalation	Human and animal	Carcinogenic

Reproductive Toxicity

Reproductive and/or Developmental Effects

Name	Route	Value	Species	Test Result	Exposure Duration
Talc	Ingestion	Not classified for development	Rat	NOAEL 1,600 mg/kg	during organogenesis

Target Organ(s)

Specific Target Organ Toxicity - single exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
------	-------	-----------------	-------	---------	-------------	-------------------

Lubricant	Inhalation	respiratory irritation	Some positive data exist, but the data are not sufficient for classification		NOAEL Not available	
-----------	------------	------------------------	--	--	---------------------	--

Specific Target Organ Toxicity - repeated exposure

Name	Route	Target Organ(s)	Value	Species	Test Result	Exposure Duration
Talc	Inhalation	pneumoconiosis	Causes damage to organs through prolonged or repeated exposure	Human	NOAEL Not available	occupational exposure
Talc	Inhalation	pulmonary fibrosis respiratory system	Not classified	Rat	NOAEL 18 mg/m3	113 weeks
Quartz Silica	Inhalation	silicosis	Causes damage to organs through prolonged or repeated exposure	Human	NOAEL Not available	occupational exposure

Aspiration Hazard

For the component/components, either no data are currently available or the data are not sufficient for classification.

Please contact the address or phone number listed on the first page of the SDS for additional toxicological information on this material and/or its components.

SECTION 12: Ecological information

Ecotoxicological information

Please contact the address or phone number listed on the first page of the SDS for additional ecotoxicological information on this material and/or its components.

Chemical fate information

Please contact the address or phone number listed on the first page of the SDS for additional chemical fate information on this material and/or its components.

SECTION 13: Disposal considerations

13.1. Disposal methods

Dispose of contents/ container in accordance with the local/regional/national/international regulations.

Prior to disposal, consult all applicable authorities and regulations to insure proper classification. The substrate that was abraded must be considered as a factor in the disposal method for this product. Dispose of waste product in a permitted industrial waste facility. As a disposal alternative, incinerate in a permitted waste incineration facility. Proper destruction may require the use of additional fuel during incineration processes. If no other disposal options are available, waste product may be placed in a landfill properly designed for industrial waste.

EPA Hazardous Waste Number (RCRA): Not regulated

SECTION 14: Transport Information

Not regulated per U.S. DOT, IATA or IMO.

These transportation classifications are provided as a customer service. As the shipper YOU remain responsible for complying with all applicable laws and regulations, including proper transportation classification and packaging. 3M transportation classifications are based on product formulation, packaging, 3M policies and 3M understanding of applicable current regulations. 3M does not guarantee the accuracy of this classification information. This information applies only to transportation classification and not the packaging, labeling, or marking requirements. The original 3M package is certified for U.S. ground shipment only. If you are shipping by air or ocean, the package may not meet applicable regulatory requirements.

SECTION 15: Regulatory information

15.1. US Federal Regulations

Contact 3M for more information.

EPCRA 311/312 Hazard Classifications:

Physical Hazards

Not applicable

Health Hazards

Not applicable

15.2. State Regulations

Contact 3M for more information.

15.3. Chemical Inventories

This product is an article as defined by TSCA regulations, and is exempt from TSCA Inventory listing requirements.

Contact 3M for more information.

15.4. International Regulations

Contact 3M for more information.

This SDS has been prepared to meet the U.S. OSHA Hazard Communication Standard, 29 CFR 1910.1200.

SECTION 16: Other information

NFPA Hazard Classification

Health: 0 **Flammability:** 1 **Instability:** 0 **Special Hazards:** None

National Fire Protection Association (NFPA) hazard ratings are designed for use by emergency response personnel to address the hazards that are presented by short-term, acute exposure to a material under conditions of fire, spill, or similar emergencies. Hazard ratings are primarily based on the inherent physical and toxic properties of the material but also include the toxic properties of combustion or decomposition products that are known to be generated in significant quantities.

HMIS Hazard Classification

Health: 0 **Flammability:** 1 **Physical Hazard:** 0 **Personal Protection:** X - See PPE section.

Hazardous Material Identification System (HMIS® IV) hazard ratings are designed to inform employees of chemical hazards in the workplace. These ratings are based on the inherent properties of the material under expected conditions of normal use and are not intended for use in emergency situations. HMIS® IV ratings are to be used with a fully implemented HMIS® IV program. HMIS® is a registered mark of the American Coatings Association (ACA).

Document Group: 26-6692-3

Version Number: 1.19

Issue Date: 03/05/18

Supersedes Date: 05/19/15

DISCLAIMER: The information in this Safety Data Sheet (SDS) is believed to be correct as of the date issued. 3M MAKES NO WARRANTIES, EXPRESSED OR IMPLIED, INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE OR COURSE OF PERFORMANCE OR USAGE OF TRADE. User is responsible for determining whether the 3M product is fit for a particular purpose and suitable for user's method of use or application. Given the variety of factors that can affect the use and application of a 3M product, some of

which are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for user's method of use or application.

3M provides information in electronic form as a service to its customers. Due to the remote possibility that electronic transfer may have resulted in errors, omissions or alterations in this information, 3M makes no representations as to its completeness or accuracy. In addition, information obtained from a database may not be as current as the information in the SDS available directly from 3M

3M USA SDSs are available at www.3M.com