

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

1 Identification

- **Product identifier**
- **Trade name:** Starrett Granite Surface Plate Cleaner
- **Recommended use and restriction on use**
- **Recommended use:** Surface cleanser
- **Restrictions on use:** Contact manufacturer
- **Details of the supplier of the Safety Data Sheet**
- **Manufacturer/Supplier:**
The L.S. Starrett Company
121 Crescent St.
Athol, MA 01331
(978) 249-3551
- **Emergency telephone number:**
ChemTel Inc.
+1 (800)255-3924, +1 (813)248-0585

2 Hazard(s) identification

- **Classification of the substance or mixture**
The product is not classified as hazardous according to the Globally Harmonized System (GHS).

- **Label elements**
- **GHS label elements** Not regulated.
- **Hazard pictograms:** Not regulated.
- **Signal word:** Not regulated.
- **Hazard statements:** Not regulated.
- **Classification system**
- **NFPA ratings (scale 0 - 4)**



- **HMIS-ratings (scale 0 - 4)**

HEALTH	1	Health = 1
FIRE	1	Fire = 1
REACTIVITY	0	Reactivity = 0

3 Composition/information on ingredients

- **Chemical characterization:** Mixtures

· Components:

34590-94-8	(2-methoxymethylethoxy)propanol	Flam. Liq. 4, H227	1-2.5%
68439-46-3	alcohols, C9-11, ethoxylated	Eye Dam. 1, H318	≤1%

(Cont'd. on page 2)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 1)

- **Additional information:** For the wording of the listed Hazard Statements refer to section 16.

4 First-aid measures

- **Description of first aid measures**
- **General information:** Take affected persons out into the fresh air.
- **After inhalation:** Supply fresh air; consult doctor in case of complaints.
- **After skin contact:**
Immediately rinse with water.
If skin irritation continues, consult a doctor.
- **After eye contact:**
Remove contact lenses if worn.
Rinse opened eye for several minutes under running water. If symptoms persist, consult a doctor.
- **After swallowing:**
Rinse out mouth and then drink plenty of water.
Do not induce vomiting; immediately call for medical help.
- **Most important symptoms and effects, both acute and delayed:**
Gastric or intestinal disorders
Coughing
Nausea
Slight irritant effect on skin and mucous membranes.
Slight irritant effect on eyes.
- **Danger:** No relevant information available.
- **Indication of any immediate medical attention and special treatment needed:**
No relevant information available.

5 Fire-fighting measures

- **Extinguishing media**
- **Suitable extinguishing agents:**
The product is not flammable.
Use fire fighting measures that suit the environment.
- **For safety reasons unsuitable extinguishing agents:** None.
- **Special hazards arising from the substance or mixture**
Formation of toxic gases is possible during heating or in case of fire.
- **Advice for firefighters**
- **Protective equipment:**
Wear self-contained respiratory protective device.
Wear fully protective suit.
- **Additional information:** No relevant information available.

6 Accidental release measures

- **Personal precautions, protective equipment and emergency procedures:**
Use respiratory protective device against the effects of fumes/dust/aerosol.
Ensure adequate ventilation.

(Cont'd. on page 3)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 2)

- Wear protective equipment. Keep unprotected persons away.
- Particular danger of slipping on leaked/spilled product.
- **Environmental precautions:** No special measures required.
- **Methods and material for containment and cleaning up:**
 - Absorb with liquid-binding material (sand, diatomite, acid binders, universal binders, sawdust).
 - Pick up mechanically.
 - Dispose contaminated material as waste according to item 13.
 - Clean the affected area carefully; suitable cleaners are:
 - Warm water
- **Reference to other sections:**
 - See Section 7 for information on safe handling.
 - See Section 8 for information on personal protection equipment.
 - See Section 13 for disposal information.

7 Handling and storage

- **Handling**
- **Precautions for safe handling:** Avoid splashes or spray in enclosed areas.
- **Information about protection against explosions and fires:** No special measures required.
- **Conditions for safe storage, including any incompatibilities**
- **Storage**
- **Requirements to be met by storerooms and receptacles:**
 - Avoid storage near extreme heat, ignition sources or open flame.
- **Information about storage in one common storage facility:**
 - Do not store together with oxidizing and acidic materials.
 - Store away from foodstuffs.
- **Further information about storage conditions:** Store in cool, dry conditions in well sealed receptacles.
- **Specific end use(s):** No relevant information available.

8 Exposure controls/personal protection

- **Control parameters**
- **Components with limit values that require monitoring at the workplace:**
 - The following constituent is the only constituent of the product which has a PEL, TLV or other recommended exposure limit.
 - At this time, the remaining constituent has no known exposure limits.

34590-94-8 (2-methoxymethylethoxy)propanol

PEL (USA)	Long-term value: 600 mg/m ³ , 100 ppm Skin
REL (USA)	Short-term value: 900 mg/m ³ , 150 ppm Long-term value: 600 mg/m ³ , 100 ppm Skin

(Cont'd. on page 4)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 3)

TLV (USA)	Short-term value: 909 mg/m ³ , 150 ppm Long-term value: 606 mg/m ³ , 100 ppm Skin
EL (Canada)	Short-term value: 150 ppm Long-term value: 100 ppm Skin
EV (Canada)	Short-term value: 910 mg/m ³ , 150 ppm Long-term value: 605 mg/m ³ , 100 ppm
LMPE (Mexico)	Short-term value: 150 ppm Long-term value: 100 ppm PIEL

- **Exposure controls**

- **Personal protective equipment:**

- **General protective and hygienic measures:**

The usual precautionary measures for handling chemicals should be followed.

Keep away from foodstuffs, beverages and feed.

Wash hands before breaks and at the end of work.

Do not inhale gases / fumes / aerosols.

Avoid contact with the eyes and skin.

- **Engineering controls:** Provide adequate ventilation.

- **Breathing equipment:**

Not required under normal conditions of use.

Use suitable respiratory protective device when aerosol or mist is formed.

For spills, respiratory protection may be advisable.

- **Protection of hands:**

Gloves not required under normal conditions of use.

Wear protective gloves to handle contents of damaged or leaking units.

The glove material has to be impermeable and resistant to the product/ the substance/ the preparation.

Selection of the glove material on consideration of the penetration times, rates of diffusion and the degradation

- **Material of gloves**

The selection of the suitable gloves does not only depend on the material, but also on further marks of quality and varies from manufacturer to manufacturer. As the product is a preparation of several substances, the resistance of the glove material can not be calculated in advance and has therefore to be checked prior to the application.

- **Penetration time of glove material**

The exact break through time has to be found out by the manufacturer of the protective gloves and has to be observed.

- **Eye protection:**



Safety glasses

- **Body protection:**

Not required under normal conditions of use.

Protection may be required for spills.

(Cont'd. on page 5)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 4)

- **Limitation and supervision of exposure into the environment** No special requirements.
- **Risk management measures** No special requirements.

9 Physical and chemical properties

· Information on basic physical and chemical properties

· Appearance:

Form: Liquid
Color: Colorless

· Odor: Odorless

· Odor threshold: Not determined.

· pH-value: Alkaline

· Melting point/Melting range: Not determined.

· Boiling point/Boiling range: >100 °C (>212 °F)

· Flash point: >94 °C (>201 °F)

· Flammability (solid, gaseous): Not applicable.

· Auto-ignition temperature: Not determined.

· Decomposition temperature: Not determined.

· Danger of explosion: Product does not present an explosion hazard.

· Explosion limits

Lower: Not determined.

Upper: Not determined.

· Vapor pressure: Not determined.

· Density at 20 °C (68 °F): 1.005-1.020 g/cm³ (8.387-8.512 lbs/gal)

· Relative density: Not determined.

· Vapor density: Not determined.

· Evaporation rate: Not determined.

· Solubility in / Miscibility with

Water: Soluble.

· Partition coefficient (n-octanol/water): Not determined.

· Viscosity

Dynamic: Not determined.

Kinematic: Not determined.

· Other information: No relevant information available.

10 Stability and reactivity

- **Reactivity:** No relevant information available.

(Cont'd. on page 6)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 5)

- **Chemical stability:**
- **Thermal decomposition / conditions to be avoided:**
No decomposition if used and stored according to specifications.
- **Possibility of hazardous reactions:**
Reacts with strong oxidizing agents.
Reacts with strong acids.
- **Conditions to avoid:** Store away from oxidizing agents.
- **Incompatible materials:** No relevant information available.
- **Hazardous decomposition products:**
Possible in traces.
Carbon monoxide and carbon dioxide
Aldehyde
Nitrogen oxides (NOx)

11 Toxicological information

- **Information on toxicological effects**
- **Acute toxicity:**
- **LD/LC50 values that are relevant for classification:** None.
- **Primary irritant effect:**
- **On the skin:** Slight irritant effect on skin and mucous membranes.
- **On the eye:** Slight irritant effect on eyes.
- **Sensitization:** No sensitizing effects known.

· IARC (International Agency for Research on Cancer):
--

None of the ingredients are listed.

· NTP (National Toxicology Program):

None of the ingredients are listed.

· OSHA-Ca (Occupational Safety & Health Administration):

None of the ingredients are listed.

- **Probable route(s) of exposure:**
Ingestion.
Inhalation.
Eye contact.
Skin contact.
- **Acute effects (acute toxicity, irritation and corrosivity):** From product as supplied: None.
- **Repeated dose toxicity:** From product as supplied: None.
- **CMR effects (carcinogenicity, mutagenicity and toxicity for reproduction)**
- **Germ cell mutagenicity:** Based on available data, the classification criteria are not met.
- **Carcinogenicity:** Based on available data, the classification criteria are not met.
- **Reproductive toxicity:** Based on available data, the classification criteria are not met.
- **STOT-single exposure:** Based on available data, the classification criteria are not met.
- **STOT-repeated exposure:** Based on available data, the classification criteria are not met.
- **Aspiration hazard:** Based on available data, the classification criteria are not met.

(Cont'd. on page 7)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 6)

12 Ecological information

- **Toxicity**
- **Aquatic toxicity** No relevant information available.
- **Persistence and degradability** Biodegradable.
- **Bioaccumulative potential:** Does not accumulate in organisms
- **Mobility in soil:** No relevant information available.
- **Ecotoxical effects:**
- **Remark:** After neutralization a reduction of the harming action may be recognized
- **Additional ecological information**
- **General notes:**
Negative ecological effects are, according to the current state of knowledge, not expected.
- **Results of PBT and vPvB assessment**
- **PBT:** Not applicable.
- **vPvB:** Not applicable.
- **Other adverse effects:** No relevant information available.

13 Disposal considerations

- **Waste treatment methods**
- **Recommendation:**
Smaller quantities can be disposed of with household waste.
Small amounts may be diluted with plenty of water and washed away. Dispose of bigger amounts in accordance with Local Authority requirements.
The user of this material has the responsibility to dispose of unused material, residues and containers in compliance with all relevant local, state and federal laws and regulations regarding treatment, storage and disposal for hazardous and nonhazardous wastes.
- **Uncleaned packagings**
- **Recommendation:** Disposal must be made according to official regulations.
- **Recommended cleansing agent:** Water, if necessary with cleansing agents.

14 Transport information

- | | |
|-------------------------------------|----------------|
| · UN-Number | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · UN proper shipping name | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · Transport hazard class(es) | |
| · DOT, ADR, IMDG, IATA | |
| · Class | Not regulated. |

(Cont'd. on page 8)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 7)

- | | |
|--|-----------------|
| · Packing group | |
| · DOT, ADR, IMDG, IATA | Not regulated. |
| · Environmental hazards | |
| · Marine pollutant: | No |
| · Special precautions for user | Not applicable. |
| · Transport in bulk according to Annex II of MARPOL73/78 and the IBC Code | Not applicable. |

15 Regulatory information

- **Safety, health and environmental regulations/legislation specific for the substance or mixture**
- **United States (USA)**
- **SARA**

· **Section 355 (extremely hazardous substances):**

None of the ingredients are listed.

· **Section 313 (Specific toxic chemical listings):**

None of the ingredients are listed.

· **TSCA (Toxic Substances Control Act)**

All ingredients are listed.

· **Proposition 65 (California)**

· **Chemicals known to cause cancer:**

None of the ingredients are listed.

· **Chemicals known to cause reproductive toxicity for females:**

None of the ingredients are listed.

· **Chemicals known to cause reproductive toxicity for males:**

None of the ingredients are listed.

· **Chemicals known to cause developmental toxicity:**

None of the ingredients are listed.

· **Carcinogenic categories**

· **EPA (Environmental Protection Agency):**

None of the ingredients are listed.

· **IARC (International Agency for Research on Cancer):**

None of the ingredients are listed.

· **NIOSH-Ca (National Institute for Occupational Safety and Health):**

None of the ingredients are listed.

· **Canadian Domestic Substances List (DSL):**

All ingredients are listed.

(Cont'd. on page 9)

Safety Data Sheet

acc. to OSHA HCS (29 CFR 1910.1200) and WHMIS 2015 regulations

Printing date: 04/22/2016

Revision: 04/22/2016

Trade name: Starrett Granite Surface Plate Cleaner

(Cont'd. of page 8)

Chemical safety assessment: A Chemical Safety Assessment has not been carried out.

16 Other information

This information is based on our present knowledge. However, this shall not constitute a guarantee for any specific product features and shall not establish a legally valid contractual relationship.

· **Date of preparation / last revision** 04/22/2016 / -

· **Abbreviations and acronyms:**

ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road

IMDG: International Maritime Code for Dangerous Goods

DOT: US Department of Transportation

IATA: International Air Transport Association

GHS: Globally Harmonised System of Classification and Labelling of Chemicals

CAS: Chemical Abstracts Service (division of the American Chemical Society)

DNEL: Derived No-Effect Level (REACH)

PNEC: Predicted No-Effect Concentration (REACH)

LC50: Lethal concentration, 50 percent

LD50: Lethal dose, 50 percent

PBT: Persistent, Bioaccumulative and Toxic

SVHC: Substances of Very High Concern

vPvB: very Persistent and very Bioaccumulative

Flam. Liq. 4: Flammable liquids, Hazard Category 4

Eye Dam. 1: Serious eye damage/eye irritation, Hazard Category 1

· **Sources**

SDS Prepared by:

ChemTel Inc.

1305 North Florida Avenue

Tampa, Florida USA 33602-2902

Toll Free North America 1-888-255-3924 Intl. +01 813-248-0573

Website: www.chemtelinc.com